



# OMSTAT ELASTIC ANTI-STATIC CORD E210

ANTISTATIC SOLUTIONS



Omstat elastic anti-static cord E210 uses highly conductive fibers to successfully eliminate static electricity.

The thousands of micropoints of the conductive fibers are charged by induction, ionize the surrounding air and neutralize the static charges of the material. It works well in many different industrial applications and is very simple to operate.



To neutralize the moving material, position the E210 across it and ground it. We position it similarly to how we position anti-static brushes. The same guidelines are in effect.

| E210 | Size | Resistance (Ω)  | Elongation (%) | Packing  |
|------|------|-----------------|----------------|----------|
|      | 2mm  | 10 <sup>3</sup> | 100%           | 10m/roll |



#### APPLICATIONS

- ▶ Packaging
- ▶ Oil Sampling
- ▶ Plastics
- ▶ Printing



**CONTACT US**

**OMSTAT**

Afroditi 1, P.O. Box 2856, GR 19400 Koropi Athens, Greece, Tel: +30 22910 70 832, Fax: +30 22910 70 897

Email: info@omstat.gr

Visit us to [www.omstat-brushes.com](http://www.omstat-brushes.com)

